


0.04 - 1.0 OD, 50mm, Apodizing Filter Bull's Eye



Bullseye Filter

Stock #64-389 3-4 DAYS



1



€379,00

ADD TO CART

Qty 1-10

€379,00

Qty 11+

€340,20

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.20

Optical Density OD (Average):
0.04 - 1.0

Substrate: [B270](#)

Type of Filter: Bull's Eye
Coating: Variable
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.10
Type: Apodizing Filter
Linearity (%): ±5 of Optical Density
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View