

## 0.125" Travel, XYZ Axes, Micro Series with Covered Rails (A)



Stock #56-418 [CONTACT US](#)

⊖ 1 ⊕ €910.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€910,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**  
With Covered Rails **Note:**

### Physical & Mechanical Properties

Linear (X-Y-Z) **Type of Movement:**

Ball Bearing	<b>Guide System:</b>
Center Drive	<b>Drive Orientation:</b>
14.2 x 26.2	<b>Stage Size (mm):</b>
3.1	<b>Travel (mm):</b>
0.125	<b>Travel (inches):</b>
0.275" (7.0mm) Thru with 5/16-24 TPI Thread	<b>Center Hole:</b>
Aluminum Body, Stainless Steel Rails	<b>Construction:</b>
0.25	<b>Load Capacity, Normal (kg):</b>
0.56 x 1.03	<b>Stage Size (inches):</b>
1.5	<b>Straight Line Accuracy (µm):</b>
12	<b>Weight (g):</b>

### Optical Properties

0.01	<b>Wobble (mrad):</b>
------	-----------------------

### Hardware & Interface Connectivity

Fine Screw (80 Pitch)	<b>Type of Drive:</b>
-----------------------	-----------------------

### Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Compliant</a>	<b>REACH 241:</b>

## Product Details

- Two Micro Sizes Available
- Versions with Covered Rails
- Three Travel Selections
- X, XY, and XYZ Axis Models

These stages are a dimensional breakthrough and the smallest positioners available today. Positive spring loaded carriage provides precise, smooth motion with no backlash. Straight line accuracy under 2 microns. Features fine 80 TPI lead screw drive. The larger series, Stage Size B, are for longer travel, higher load applications. Fully metric compatible clearance holes. Covered Rail versions are slightly wider, but offer protection for the guide rails. Accessories allow for mounting our precision pinholes for spatial filtering applications. Anodized aluminum construction with stainless rails.

## Technical Information

