

[See all 4 Products in Family](#)

## 0.19 - 20µm, 250W, VIS/NIR Portable Laser Power Meter



0.19 - 20µm, 250W, VIS/NIR Portable Laser Power Meter

Stock **#78-470** NEW **1 In Stock**

- 1 + €1.360<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-4        | €1.360,00 each                |
| Qty 5+         | €1.225,00 each                |
| Need More?     | <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Product Downloads

| General                              |                             |
|--------------------------------------|-----------------------------|
| 17                                   | Operating Lifetime (hours): |
| 1.50                                 | Response Time (s):          |
| Touch screen color LCD               | Type of Display:            |
| USB Port Available for Data Transfer | Note:                       |

| Physical & Mechanical Properties   |                              |
|------------------------------------|------------------------------|
| 181.40                             | Length (mm):                 |
| 210                                | Weight (g):                  |
| 59.00                              | Width (mm):                  |
| 17.00                              | Depth (mm):                  |
| Optical Properties                 |                              |
| 248 - 2500                         | Wavelength Range (nm):       |
| 0.248 - 2.5                        | Wavelength Range (µm):       |
| 0.193 - 20µm                       | Spectral Range:              |
| 0.248 -2.5µm                       | Calibrated Spectral Range:   |
| Sensor                             |                              |
| 5s                                 | Exposure Time:               |
| Electrical                         |                              |
| 10                                 | Noise Equivalent Power (mW): |
| Hardware & Interface Connectivity  |                              |
| USB Rechargeable Battery           | Power Supply:                |
| Threading & Mounting               |                              |
| 2 x 8-32                           | Mounting Hole for Screw:     |
| Environmental & Durability Factors |                              |
| 65                                 | Maximum Temperature (°C):    |
| Regulatory Compliance              |                              |
| <a href="#">View</a>               | Certificate of Conformance:  |

## Product Details

- Small Portable Design with Touchscreen Display
- Computer and Software Not Required
- High Damage Threshold
- USB Rechargeable Battery

Touchscreen Portable Laser Power Meters feature LCD displays with touchscreen controls, the ability to adjust wavelength, brightness and screen orientation, and min/max display. Available in two designs, one as a silicon based sensor and the other an absorber, these portable power meters can transfer data to a computer for data logging via a mini USB port. The silicon sensor model (#34-514) features a folding body design with a click stop at 90 degrees, providing the unique ability of being placed on an optical table unmounted when oriented at 90 degrees. If the beam height is 78mm off the optical table, you can simply set the folded power meter directly onto the table. Both Touchscreen Portable Laser Power Meter models feature 8-32 mounting holes for table top mounting and rechargeable battery.

**Note:** Mini-USB cable not included.