

# 0.2 x 40° Diffusing Angle 8" x 8" Unmounted



Stock **#48-000** CLEARANCE 3-4 DAYS

-

1

+

**€457,50**

ADD TO CART

|         |
|---------|
| Qty 1+  |
| €457,50 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Angle Tolerance (°):**  
±0.5 x ±4

**Diffusing Angle (°):**  
0.2 x 40 (FWHM)

**Dimensional Tolerance (mm):**  
±0.5

**Dimensions (inches):**  
8 x 8

**Dimensions (mm):**  
203.20 x 203.20

|                                                                                                          |
|----------------------------------------------------------------------------------------------------------|
| <div>Operating Temperature (°C):<br/>-30 to +100 (Maximum of 240 Hours)</div>                            |
| <div>Substrate: <input type="checkbox"/><br/>Polycarbonate</div>                                         |
| <div>Thickness (mm):<br/>0.78</div>                                                                      |
| <div>Transmission (%):<br/>&gt;85</div>                                                                  |
| <div>Type:<br/>Holographic Diffuser</div>                                                                |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                                                          |
| <div>Width (mm):<br/>203.20</div>                                                                        |
| <div>Construction:<br/>Unmounted</div>                                                                   |
| <div>Damage Threshold, By Design: <input type="checkbox"/><br/>0.22 J/cm² @ 1064nm, 10ns (typical)</div> |
| <div>Length (mm):<br/>203.20</div>                                                                       |

Regulatory Compliance

|                                                                 |
|-----------------------------------------------------------------|
| <div>RoHS 2015:<br/><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:<br/><a href="#">View</a></div> |
| <div>Reach 233:<br/><a href="#">Compliant</a></div>             |