

[See all 11 Products in Family](#)

## 0.25" Travel, 0.001" Grad. Mic. Drive S-Face



Drive Mechanisms

Stock **#87-093** **1 In Stock**

⊖ 1 ⊕ €86.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	€86,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

#### General

English **Type:**

Mitutoyo **Manufacturer:**

148-206-10 **Model Number:**

#### Physical & Mechanical Properties

**Travel (inches):**

0.25

**Graduation (inches):**

0.001

**Stem Diameter (mm):**

3.5

**Stem/Spindle:**

Plain/Spherical

**Stem Length (mm):**

5

**Spindle Diameter (mm):**

2

**Min. Spindle Length (mm):**

6.5

**Max. Diameter (mm):**

6

**Overall Length (mm):**

32

## Hardware & Interface Connectivity

**Type of Drive:**

English Micrometer

## Regulatory Compliance

**RoHS 2015:**

[Exempt](#)

**Certificate of Conformance:**

[View](#)

**REACH 241:**

[Contains SVHC\(s\)](#)

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

;