

# 0.3 OD M49.0 x 0.75, Mounted Absorptive ND Filter



Stock **#54-729** 3-4 DAYS

- 1 + **€43,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €43,00                        |
| Qty 10+                       |
| €39,50                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):  
0.3

Clear Aperture CA (mm):  
45.0

Filter Thread:  
M49 x0.75

Substrate: ☐

|                                                                |
|----------------------------------------------------------------|
| ND Filter Glass                                                |
| Thickness with Mount (mm):<br>5.00                             |
| Surface Quality:<br>80-50                                      |
| Transmission (%):<br>50                                        |
| Type:<br>Mounted Imaging Filter                                |
| Blocking Wavelength Range (nm):<br>400 - 700                   |
| Mount Thickness (mm):<br>3.8 ±0.1                              |
| Note:<br>AR Coating: MgF <sub>2</sub>                          |
| Coating Specification:<br>R <sub>avg</sub> ≤1.75% @400 - 700nm |
| Mount Diameter (mm):<br>51.0 +0/-0.2                           |
| Mount Thickness Including Threads (mm):<br>6.3                 |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Exempt</a>                     |
| Certificate of Conformance:<br><a href="#">View</a> |