

TECHSPEC® 0.5mm Thick, C-Mount Brass Spacer Ring



Brass Spacer Ring

Stock #03-631 **20+ In Stock**

⊖ 1 ⊕ €11²⁵

ADD TO CART

Volume Pricing

Qty 1-4	€11,25 each
Qty 5-9	€10,50 each
Qty 10-25	€10,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spacer Ring

Function:

Physical & Mechanical Properties

29.0

Outer Diameter (mm):

Thickness (mm):

0.50

Inner Diameter (mm):

25.5

Threading & Mounting

Thread Type:

C-Mount

Regulatory Compliance

RoHS 2015:

[Exempt](#)

Certificate of Conformance:

[View](#)

Reach 247:

[Contains SVHC\(s\)](#)

Product Details

- Fit Over Male C, S, and T-Mount Threads
- Wide Range of Thicknesses Available for Accurate Spacing
- Spacer Ring Kits Available

TECHSPEC® C, S, and T-Mount Brass Spacer Rings fit over the male threads on our C, S, and T-Mount components, extending the overall length of the system. These spacer rings are ideal for making incremental adjustments to component spacing within an optical system. TECHSPEC® C, S, and T-Mount Brass Spacer Rings are available in thicknesses ranging from 0.25mm to 2.0mm, ensuring that application specific spacing is available. Kits of [C-Mount](#) and [S-Mount](#) Spacer Rings with 2 of each size can be found under the "Accessories" tab for this product. These spacer rings can be combined in multiple configurations to achieve the desired spacing distance.

Technical Information

