

0.5" x 0.5" (200 lp/mm), Ronchi Ruling



Stock **#66-345** 3-4 DAYS

- 1 + **€300,00**

ADD TO CART

Qty 1-4
€300,00

Qty 5+
€285,80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
200

Substrate:

Float Glass
Optical Density OD (Average): 3.00
Dimensions (inches): 0.5 x 0.5
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View