

0.5" x 6.00", 0.25" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-107** 20+ In Stock

-

1

+

€53⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	€53,00 each
Qty 11-49	€48,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Fresnel Lens	Type:
Physical & Mechanical Properties	
0.06	Center Thickness CT (inches):
±0.05	Dimensional Tolerance (inches):

0.5 x 6.0	Dimensions (inches):
12.7 x 152.4	Dimensions (mm):
0.25 x 6.0	Effective Size (inches):
±0.020	Thickness Tolerance (inches):

Optical Properties

6.35	Effective Focal Length EFL (mm):
Acrylic	Substrate: ☐
Uncoated	Coating:
400 - 1100	Wavelength Range (nm):
0.25	Effective Focal Length EFL (inches):
200.00	Groove Density (grooves/inch):
1.49	Index of Refraction (n _d):
85 (Typical)	Transmission (%):

Environmental & Durability Factors

80 (Maximum)	Operating Temperature (°C):
--------------	-----------------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

