

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



Stock #49-072 CLEARANCE 3-4 DAYS

-

1

+

 €50,00

ADD TO CART

Qty 1-5

€50,00

Qty 6+

€40,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°):
0

Optical Density OD (Average):
0.6

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%): 37.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%): 25.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant