

0.6 OD M55.0 x 0.75, Mounted Absorptive ND Filter



Stock **#65-018** CLEARANCE 3-4 DAYS

-

1

+

€38,95

ADD TO CART

Qty 1+
€38,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average): 0.6
Clear Aperture CA (mm): 51.0
Filter Thread: M55 x0.75
Substrate: ND Filter Glass
Thickness with Mount (mm): 5.00

Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 57.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View