

0.6 OD M72 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-598** [CONTACT US](#)

- 1 + **€125,00**

ADD TO CART

Qty 1-9
€125,00

Qty 10+
€119,60

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
67.50

Filter Thread:
M72 x0.75

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 25.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View