

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

0.65" X 5.95" , 0.38" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-108 3-4 DAYS



1



€46,00

ADD TO CART

Qty 1-10

€46,00

Qty 11+

€40,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
9.65

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.06
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 0.65 x 5.95
Dimensions (mm): 16.51 x 151.13
Effective Focal Length EFL (inches): 0.38
Effective Size (inches): 0.38 x 5.95
Groove Density (grooves/inch): 200.00
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Transmission (%): 85 (Typical)
Thickness Tolerance (inches): ±0.020

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View