

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

0.65X - 4.6X Dynamic Focus VZM™ Lens



Dynamic Focus VZM™ Lens

Stock #89-999 CLEARANCE 3-4 DAYS



1



€1.456,95

ADD TO CART

Qty 1+

€1.456,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
248.00

Filter Thread:
M22.5 x 0.50

Working Distance Tolerance (mm):
±3

Zoom Ratio:
7:1

Type:

Zoom Lens
Primary Magnification PMAG: 0.65X - 4.6X
Maximum Sensor Format: 2/3"
Working Distance (mm): 87.00
Style: Liquid Lens
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View