

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

0.9 OD M25.5 X 0.50, Mounted Absorptive ND Filter



Stock #59-173 [CONTACT US](#)

-

1

+

€38,50

ADD TO CART

Qty 1-9
€38,50
Qty 10+
€37,50
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average): 0.9
Clear Aperture CA (mm): 21.0
Filter Thread: M25.5 x0.50
Substrate: ☐

ND Filter Glass
Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 27.5 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View