

0.9 OD M43 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-701 3-4 DAYS

- 1 + **€67,50**

ADD TO CART

Qty 1-9
€67,50

Qty 10+
€64,80

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
38.00

Filter Thread:
M43 x0.75

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 12.50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View