

0.9 OD M46.0 x 0.75, Mounted Absorptive ND Filter

0.9 OD M46.0 x 0.75, Mounted Absorptive ND Filter



Stock #54-740 3-4 DAYS

⊖ 1 ⊕ €43,00

ADD TO CART

Qty 1-9	
€43,00	

Qty 10+	
€39,50	

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
42.0

Filter Thread:
M46 x0.75

Substrate: ☐

ND Filter Glass
Thickness with Mount (mm): 5.00
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 4.4 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 48.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.4

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View