

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



PlatinumTL[™] Telecentric Lenses



Stock #16-750 3-4 DAYS



1



€2.460,00

ADD TO CART

Qty 1+

€2.460,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View, 28.7mm Sensor:
31.9mm

Length (mm):
198.78

Horizontal Field of View, 1/2" Sensor:
7.1mm

Horizontal Field of View, 2/3" Sensor:

9.8mm
Filter Thread: M62 x0.75 (Female)
Maximum Diameter (mm): 65.0
Horizontal Field of View, 1" Sensor: 14.2mm
Maximum Image Circle (mm): 28.70
Numerical Aperture NA, Object Side: 0.045
Stock No. of Mounting Clamp: #56-025 Sold Separately
Flange Distance (mm): 17.5
Horizontal Field of View, 4/3" Sensor: 19.2mm
Horizontal Field of View, 1.1" Sensor: 15.8mm
Number of Elements (Groups): 10 (7)
Typical Telecentricity @ 588nm (°): <0.070
Typical Distortion @ 588nm (%): <0.035
Type: Telecentric Lens
Primary Magnification PMAG: 0.9X
Maximum Sensor Format: APS-C
Working Distance (mm): 111.00
Mount: TFL-Mount
Aperture (f/#): f/6 - f/22
Coating: 425 - 675nm BBAR
Depth of Field (mm): ±0.65 at f/10 (20% @ 20 lp/mm)
Horizontal Field of View, APS-C Sensor: 24.9mm
FOV @ Max Sensor Format, H x V (mm): 24.9 x 18.7
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View