

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 0° AOI, 25.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock #64-458 3-4 DAYS



1



€53,00

ADD TO CART

Qty 1-9

€53,00

Qty 10+

€46,70

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Coating:
Hot Mirror, 0°

Substrate:
BOROFLOAT®

Dimensions (mm): 25.0 x 25.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): +0.0/-0.2
Coating Specification: T _{avg} >90% @ 400 - 690nm, R _{avg} >95% @ 710 - 1150nm AR: R _{avg} <1% @ 400 - 700nm
Wavelength Range (nm): 400 - 1150
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant