

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

T-128, 101.6 X 101.6mm NBS 1963A Positive Target



NBS 1963A Resolution Target

Stock #85-276 3-4 DAYS



1



€242,00

ADD TO CART

Qty 1-4

€242,00

Qty 5+

€230,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
Vacuum deposited durable chromium pattern

Frequency (lp/mm):
1-128

Substrate:
Float Glass

Optical Density OD (Average): ≥3.0
Pattern Size (mm): 42.0 x 40.5
Dimensions (mm): 101.6 x 101.6
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.100
Type: Positive
Dimensional Tolerance (mm): ±0.100
Note: Pattern Location is Centered
NIST Certification: No
Changes in Frequency Steps: 1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0 , 4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0, 16.0, 18.0, 20.0, 23.0, 26.0, 29.0, 32.0, 40.0, 45.0, 51.0, 57.0, 64.0, 72.0, 80.0, 90.0, 101.0, 114, 128
Line Width Tolerance (µm): ±12.1 - 1.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant