

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

10 X 10mm 120 Grit Ground Glass Diffuser



Stock #83-083 3-4 DAYS

- 1 + €17,75

ADD TO CART

Qty 1-10
€17,75
Qty 11+
€15,25
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Uncoated

Dimensional Tolerance (mm):

±0.25

Dimensions (mm):

10.00 x 10.00

Edges:

Cut Edges
Grit: 120
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 10.00
Note: Sandblasted on first surface
Length (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant