

10 x 10mm, 500µm Pitch, 3.2° Divergence, Cyl. Microlens Array



Stock **#86-844** 3-4 DAYS

- 1 + **€705,00**

ADD TO CART

Qty 1-10
€705,00

Qty 11+
€620,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
4.50

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Coating:
Uncoated

Type:

Lens Array
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.05
Dimensions (mm): 10.0 x 10.0
Divergence Angle (°): ±3.2
Pitch (µm): 500.00
Pitch Tolerance (µm): ±0.25
Radius R (mm): 2.040
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.05

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View