

100 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-879 CLEARANCE 2 In Stock

-

1

+

€486^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	€486,00 each
Qty 5+	€461,90 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads	
Physical & Mechanical Properties	
3.00	Length (inches):
12.7 x 25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):

Optical Properties	
Vacuum Deposited Chrome Fluorescent Peak Excitation @ 365 nm; Fluorescent Peak Emission @ 550 nm	Coating:
100.00	Frequency (lp/mm):
Fused Silica with Fluorescent Backing	Substrate:
3.00	Optical Density OD (Average):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.