


100 x 100mm, 0.7mm Thick, EAGLE XG® Window



Stock #18-297 3-4 DAYS

- 1 + **€44,00**

ADD TO CART

Qty 1-5
€44,00

Qty 6+
€35,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
90.00 x 90.00

Dimensions (mm): 100.00 x 100.00 ±0.25
Thickness (mm): 0.70 ±0.07
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 3.17 (0 to +300°C)
Density (g/cm³): 2.38
Edges: Cut and Seamed
Index of Refraction n_d: 1.51
Poisson's Ratio: 0.23
Substrate: EAGLE XG®
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 350 - 2000
Young's Modulus (GPa): 73.6
Length (mm): 100.00
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant