

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 100 X 100mm Linear Plastic Polarizer (XP42-200)



Stock #86-195 3-4 DAYS



1



€92,00

ADD TO CART

Qty 1+

€92,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Extinction Ratio:
9000:1

Substrate: XP42-200 on PMMA

Length (mm):
100.00

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
100.0 x 100.0 +0.0/-1.0

Thickness (mm): 2.22 ±0.25
Transmission (%): Single: 42 Parallel: 36 Crossed: <0.004
Type: Linear Polarizer
Construction: Polarizing Film on PMMA
Wavelength Range (nm): 400 - 700
Polarization Efficiency (%): >99.98
Width (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant