

100 x 150mm, Blue, EuroBrite™ Backlight

See More by [Advanced Illumination](#)



AI EuroBrite Backlight



Stock **#33-461** [CONTACT US](#)

-

1

+

€565⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€565,00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

50,000	Operating Lifetime (hours):
BL-S100150-470	Model Number:

LED Illuminator	Type of Illumination:
Advanced Illumination	Note:
	See Technical Information Tab for Typical Intensity
Backlight	Manufacturer:
	Geometry:

Strobed or Constant	Illumination Mode:
---------------------	--------------------

Physical & Mechanical Properties

150 x 139 x 30	Dimensions (mm):
253.00	Weight (g):

100 x 150	Active Area (mm):
-----------	-------------------

Optical Properties

Blue	Color:
470	Wavelength (nm):

Electrical

0.42 - 0.49A	Maximum Input Current:
10% @ 0.7V, 100% @ 10V	Analog Intensity Control:

10µm	Trigger-to-Pulse Latency:
------	---------------------------

Hardware & Interface Connectivity

Flying Leads	Connector:
24V nominal (min. 22 / max. 28)	Input Voltage (V):

Power Supply: Power Supply Required and Sold Separately: USA: #66-855 Europe: #66-855 Japan: #89-513 Korea: #33-773 China: #66-855	
--	--

Environmental & Durability Factors

0 - 60	Operating Temperature (°C):
IP67	Environmental Rating:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Contains SVHC(s)	Reach 233:
----------------------------------	------------

Product Details

- DaisyChain up to Four 100 x 150mm Units
- Requires No Heat Sink
- Available in White, Red, and Blue

Advanced Illumination EuroBrite™ Backlight illuminators feature on-board smart drivers functional during strobe and continuous operation modes making them ideal for the most demanding performance constraints. Adaptive OverDrive™ allows for power optimization while in strobing mode, and Adaptive Thermal Feedback™ gives operational current control to the user, preventing overheating and eliminating the need for a heat sink. These Advanced Illumination EuroBrite™ Backlight illuminators feature a ruggedized, sealed enclosure, and are available in white, red, or blue versions. The ability to operate four 100 x 150mm units connected to one another, and an analog dimming control operable in both strobe and continuous modes add to illuminator’s customizability.

Note: A 24V power supply is required.

Technical Information

Typical Intensity

Size	50 x 75mm	100 x 150mm
Working Distance	At Surface	At Surface
Area	58 x 38mm	124 x 91mm
Typical Irradiance (W/M²)	101	140
Typical Illuminance (kLux)	38	52

;