

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #67-187 3-4 DAYS



1



€107,00

ADD TO CART

Qty 1-10

€107,00

Qty 11+

€95,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):
150.00 @ 587.6nm

Back Focal Length BFL (mm):
136.16

Coating:

Uncoated
Substrate: N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 21.00
Edge Thickness ET (mm): 2.72
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 95
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View