

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-906 3-4 DAYS



1



€166,00

ADD TO CART

Qty 1-10

€166,00

Qty 11+

€150,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):
300.00 @ 587.6nm

Back Focal Length BFL (mm):
291.00

Coating:

MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 120-80
Center Thickness CT (mm): 12.50
Edge Thickness ET (mm): 4.21
Radius R₁ (mm): 155.00
Clear Aperture CA (mm): 97
f#: 3
Numerical Aperture NA: 0.17
Type: Condenser Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant