

100X EO M Plan Apo ULWD Infinity Corrected



50XEO MPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock **#59-882** 3-4 DAYS



1



€4.876,00

ADD TO CART

Qty 1+

€4.876,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
0.24

Horizontal Field of View, 1/2" Sensor:
0.064mm

Horizontal Field of View, 2/3" Sensor:
0.088mm

Horizontal Field of View, 1" Sensor:
0.128mm

Focal Length FL (mm):

2.00
Length (mm): 82.00
Length excluding Threads (mm): 82.00
Magnification: 100X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.55
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.5
Depth of Field (µm): 0.90
Field of View, 24 Diameter Field Eyepiece (mm): 0.24
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 13.0
Weight (g): 340.00
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View