

[All Products](#) / [Microscopy](#) / [Infinity Corrected Objectives](#) / [Mitutoyo Brightfield and Darkfield \(BD\) Infinity Corrected Objectives](#)

[See all 7 Products in Family](#)

100X Mitutoyo BD Plan Apo Objective

See More by [Mitutoyo](#)

100X Mitutoyo BD Plan Apo Objective

See More by [Mitutoyo](#)



Mitutoyo Brightfield and Darkfield (BD) Infinity Corrected Objectives

Stock #18-408 3-4 DAYS

$\ominus$ 1 $\oplus$

€4.028,00

ADD TO CART

Qty 1+

€4.028,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Focal Length FL (mm):
2.00

Model Number:
378-836-7

Length excluding Threads (mm):
89.00

Magnification: 100X
Maximum Diameter (mm): 44
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.7
Mounting Threads: M40 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 0.4
Depth of Field (µm): 0.60
Field of View, 24 Diameter Field Eyepiece (mm): 0.24
Operating Temperature (°C): +5 to +40
Working Distance (mm): 6
Weight (g): 460
Note: #18-653 or #18-652 are required for darkfield operation.
Wavelength Range (nm): 435 - 655
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View