


TECHSPEC® 101.6mm Dia. λ /10 Fused Silica Optical Flat



Stock **#01-611-000** 3-4 DAYS

⊖ 1 ⊕ **€798,00**

ADD TO CART

Qty 1-5

€798,00

Qty 6+

€718,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
 λ /10

Abbe Number (v_d):
67.8

Coating:

Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Diameter (mm): 101.60 +0.00/-1.00
Thickness (mm): 19.05 ±1.5
Diameter (inches): 4.00 +0.00/-0.04
Thickness (inches): 0.75 ±0.06
Clear Aperture CA (mm): 91.40
Color: Clear
Construction: Single Surface
Density (g/cm³): 2.20
Index of Refraction n_d: 1.458
Knoop Hardness (kg/mm²): 522
Parallelism (arcmin): ≤3
Poisson's Ratio: 0.16
Substrate: Fused Silica
Surface Quality: 60-40
Type: Interferometry Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant