

TECHSPEC® 1064nm, 25mm Diameter, Thin Film Laser Line Polarizer



TECHSPEC High Energy Laser Line Polarizers

Stock **#86-716** 3-4 DAYS



1



€505,00

ADD TO CART

Qty 1-5

€505,00

Qty 6+

€452,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
45 ±2

Clear Aperture CA (mm):
22.50

Design Wavelength DWL (nm):
1064

Diameter (mm): 25.00
Extinction Ratio: 10,000:1
Substrate: Fused Silica (Coming 7980)
Surface Quality: 40-20
Thickness (mm): 6.00
Thickness Tolerance (mm): ±0.25
Transmission (%): >98 (P-Polarization)
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.00/-0.25
Construction: Thin Film Dielectric
Clear Aperture (%): 90
Transmitted Wavefront, P-V: λ/4 @ 633nm
Damage Threshold, By Design: 2 J/cm² @ 532nm, 10ns, S or P Polarization

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant