

1064nm CWL, 2.00 FWHM, 25mm Dia.Ultra Narrow Filter



Stock #21-395 3-4 DAYS

- 1 + **€1.500,00**

ADD TO CART

Qty 1-5
€1.500,00

Qty 6+
€1.345,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.25

Angle of Incidence (°):
0

Clear Aperture CA (mm):
21.00

Center Wavelength CWL (nm): 1,064.00
Full Width-Half Max FWHM (nm): 2.00
Substrate: ☐ Soda Lime Glass & Filter Glass
Minimum Transmission (%): >55
Type: Bandpass Filter
Note: Filter Design: Two-Cavity
Substrate Thickness (mm): 6 +0.00/-0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant