

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 10mm Aluminized, Half-Penta Prism



Stock #65-587 3-4 DAYS

1 €147,50

ADD TO CART

Qty 1-5

€147,50

Qty 6+

€118,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS 0° & Aluminized

Substrate: ☐
[N-BK7](#)

Height (mm):
14.14

Surface Quality: 40-20
Type: Half-Penta Prism
Dimensional Tolerance (mm): ±0.10
Angle Tolerance (arcmin): ±3
Bevel: Protective bevel as needed
Image Orientation: Right-Handed
Coating Specification: Entrance/Exit Faces: R _{avg} ≤0.4% @ 425 - 675nm Reflecting Surface: R _{avg} >85% @ 400 - 700nm w/Black Overpaint
Ray Deviation (°): 45
Wavelength Range (nm): 425 - 675
Surface Flatness (P-V): λ/2
Width (mm): 10.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant