

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

10mm Aperture, 25mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock #88-186 3-4 DAYS



1



€310,00

ADD TO CART

Qty 1-10

€310,00

Qty 11+

€273,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.88

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Type:
Refocusing Assembly

Wavelength Range (nm): 190 - 1250
Aperture Size: 10.0
Focal Length FL (mm): 25.00
Housing Material: Anodized Aluminum
Length (mm): 16.38
Note: Compatible with #88-180 , #88-181 , #88-190 , & #88-191 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
