

10mm Aperture, 38mm FL VIS/NIR Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock **#88-184** 3-4 DAYS



1



€170,00

ADD TO CART

Qty 1-10

€170,00

Qty 11+

€150,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.88

Substrate: ☐
[N-BK7](#)

Type:
Refocusing Assembly

Wavelength Range (nm): 350 - 2200
Aperture Size: 10.0
Focal Length FL (mm): 38.00
Housing Material: Anodized Aluminum
Length (mm): 16.38
Note: Compatible with #88-180 , #88-181 , #88-190 , & #88-191 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View