

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Precision Aspheric Lenses

Stock #16-991 3-4 DAYS

[Other Coating Options](#)



1



€240,00

ADD TO CART

Qty 1-5

€240,00

Qty 6+

€192,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00 +0.00/-0.025

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Numerical Aperture NA:

0.50
Back Focal Length BFL (mm): 5.68
Substrate: ☐ N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: SWIR+ (900-1700nm)
Coating Specification: Ravg <0.5% @ 900 - 1700nm @ ±30° AOI Rabs <1.5% @ 900 - 1700nm @ ±30° AOI
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 9.00
Edge Thickness ET (mm): 6.18
Center Thickness CT (mm): 7.80 ±0.10
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 900 - 1700
Conjugate Distance: Infinite
Power (diopters): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant