

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #90-323 3-4 DAYS



1



€58,00

ADD TO CART

Qty 1-10

€58,00

Qty 11+

€48,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00

Effective Focal Length EFL (mm):
10.00 ±0.2

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm):

8.28
Substrate: □ Aton Plastic
Coating: BBAR (650-850nm)
Coating Specification: R _{abs} <1.0% @ 650 - 850nm
Clear Aperture CA (mm): 8.00
Edge Thickness ET (mm): 3.1
f/#: 1.25
Bevel: Protective bevel as needed
Flange Distance (mm): 8.28
Type: Aspheric Lens
Wavelength Range (nm): 650 - 850
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View