

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 10mm Dia X 15mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #47-754 3-4 DAYS



1



€119,00

ADD TO CART

Qty 1-5

€119,00

Qty 6+

€95,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00

Effective Focal Length EFL (mm):
15.00

Substrate: ☐
N-BK7

f/#: 1.5
Numerical Aperture NA: 0.33
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 12.82
Center Thickness CT (mm): 3.30
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.70
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 7.75
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View