

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

10mm Diameter 120 Grit Ground Glass Diffuser



Stock #83-082 ☒ In Stock

-

1

+

 €17,75

ADD TO CART

Qty 1-10
€17,75
Qty 11+
€15,25
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00 ±0.25

Coating:
Uncoated

Edges:
Ground Edges

Grit: ☐

Substrate: □
Float Glass

Thickness (mm):
1.60

Type:
Ground Glass Diffuser

Wavelength Range (nm):
350 - 2000

Note:
Sandblasted on first surface

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)

