

10mm Diameter UV Fused Silica Ground Glass Optical Diffuser



Stock #49-155 3-4 DAYS

- 1 + **€50,00**

ADD TO CART

Qty 1-10
€50,00
Qty 11+
€40,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 ±0.25

Grit: ☐
220

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 200 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant