

**TECHSPEC® 10mm H x 20mm L x 100mm FL Uncoated, Illumination Grade PCX Cylinder Lens**



Stock **#43-862** CLEARANCE 3-4 DAYS

- 1 + **€75,95**

ADD TO CART

Qty 1+

€75,95

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):  
100.00

Substrate: ☐  
[N-BK7](#)

f#:  
10

Numerical Aperture NA:  
0.05

|                                                 |
|-------------------------------------------------|
| <b>Coating:</b><br>Uncoated                     |
| <b>Type:</b><br>Cylinder Lens, Plano-Convex     |
| <b>Wavelength Range (nm):</b><br>350 - 2200     |
| <b>Back Focal Length BFL (mm):</b><br>97.92     |
| <b>Center Thickness CT (mm):</b><br>3.00        |
| <b>Center Thickness Tolerance (mm):</b><br>±0.1 |
| <b>Dimensional Tolerance (mm):</b><br>+0.0/-0.2 |
| <b>Dimensions (mm):</b><br>10.0 x 20.0          |
| <b>Edge Thickness ET (mm):</b><br>2.76          |
| <b>Focal Length Tolerance (%):</b><br>±3        |
| <b>Radius R<sub>1</sub> (mm):</b><br>51.63      |
| <b>Surface Quality:</b><br>60-40                |
| <b>Tilt Tolerance (mm):</b><br>±0.1 over H      |
| <b>Wedge Tolerance (arcmin):</b><br>15.00       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |