

TECHSPEC®

# 10mm Schmidt-Pechan Prism



TECHSPEC® Pechan Prism

Stock **#36-038** [CONTACT US](#)



1



€395,00

ADD TO CART

Qty 1-5

€395,00

Qty 6+

€316,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Coating:**  
VIS 0° & Aluminized

**Substrate:** ☐  
[N-BK7](#)

**Height (mm):**  
20.2

|                                                                                                                                                                         |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <div>Surface Quality:</div> <div>40-20</div>                                                                                                                            |
| <div>Thickness (mm):</div> <div>12.99</div>                                                                                                                             |
| <div>Type:</div> <div>Schmidt-Pechan Prism</div>                                                                                                                        |
| <div>Dimensional Tolerance (mm):</div> <div>±0.1</div>                                                                                                                  |
| <div>Image Orientation:</div> <div>Right-Handed</div>                                                                                                                   |
| <div>Coating Specification:</div> <div>Entrance/Exit Faces: R<sub>avg</sub> ≤0.4% @ 425 - 675nm<br/>Roof: R<sub>avg</sub> &gt;85% @ 400 - 700nm w/Black Overpaint</div> |
| <div>Ray Deviation (°):</div> <div>0</div>                                                                                                                              |
| <div>Wavelength Range (nm):</div> <div>400 - 700</div>                                                                                                                  |
| <div>Surface Flatness (P-V):</div> <div>λ/8</div>                                                                                                                       |
| <div>Width (mm):</div> <div>14.00</div>                                                                                                                                 |
| <div>Ray Deviation Tolerance (arcmin):</div> <div>±10</div>                                                                                                             |

Regulatory Compliance

|                                                                        |
|------------------------------------------------------------------------|
| <div>RoHS:</div> <div>Compliant</div>                                  |
| <div>Certificate of Conformance:</div> <div><a href="#">View</a></div> |