

TECHSPEC® 10mm, Uncoated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock **#45-949** ☒ In Stock

⊖

1

⊕

€144,00

ADD TO CART

Qty 1-5

€144,00

Qty 6+

€129,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-SF11](#)

Surface Quality:

20-10

Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 14.10
Length of Legs (mm): 10.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 2500
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View