

[See all 22 Products in Family](#)

10X 120i Plan APO Infinity Corrected Objectives



#15-943: 10X 120i Infinity Corrected Objective



Stock **#15-943** **1 In Stock**

- 1 + €855⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€855,00 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Compatible Tube Lens Focal Length (mm):
Focal Length: 120mm

Type:
Microscope Objective

Style:

Infinity Corrected

Manufacturer:

Edmund Optics®

Physical & Mechanical Properties

64.00 Length (mm):

64.00 Length excluding Threads (mm):

35 Maximum Diameter (mm):

130 Weight (g):

Optical Properties

0.64mm Horizontal Field of View, 1/2" Sensor:

0.88mm Horizontal Field of View, 2/3" Sensor:

1.41mm Horizontal Field of View, 1.1" Sensor:

12.00 Focal Length FL (mm):

10X Magnification:

0.28 Numerical Aperture NA:

1.0 Resolving Power (μm):

3.60 Depth of Field (μm):

14.7 Working Distance (mm):

400 - 700 Wavelength Range (nm):

17.6 Field Number (mm):

78.7 Parfocal Length (mm):

Sensor

1.1" Maximum Sensor Format:

Threading & Mounting

1" x 32 TPI Mounting Threads:

Environmental & Durability Factors

+10 to +40 Operating Temperature ($^{\circ}\text{C}$):

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Contains SVHC\(s\)](#) Reach 240:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

