


# 10X Illuminated Loupe w/ Linear Scale



Linear Scale



Stock #39-100 [CONTACT US](#)

⊖ 1 ⊕ €182.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-4	€182,00 each
Qty 5-9	€160,10 each
Qty 10+	€141,80 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

Field of View (inches):

1.00

Diameter of Included Lens (inches):

0.75

Diameter of Compatible Reticle (mm):  
35.00

Height (inches):  
1.75

## Optical Properties

Magnification:  
10X

Working Distance (inches):  
0.65

## Regulatory Compliance

Certificate of Conformance:  
[View](#)

## Product Details

### Illuminated Loupe with Scale

This magnifier is built into a fully removable flashlight-type assembly for illumination. Includes a hard-shell vinyl case. Requires two "C" batteries, not included. Unit measures 1-3/8" Dia x 7"L, weighs 3.5 oz 7X includes a 26mm diameter reticle with a scale of 0 - 20mm in 0.1mm increments. 10X includes a 35mm diameter reticle with a scale of 15 - 0 - 15mm in 0.1mm increments.

- 7X and 10X Magnifications Available
- Choose from Loupe, Illuminated Loupe and Loupe Sets
- Reticle Included with Each Option

Peak 7X or 10X Measuring Loupes come with a removable glass reticle scale placed in direct contact with the work to be measured for precise comparison. Additional [reticles](#) are also available. All models feature smooth-helicoid twist focus and fully coated achromatic lens systems for color correct flat field viewing. Peak 7X or 10X Measuring Loupes are offered in with a singular loupe, an illuminated loupe, and loupe sets. The included lens features a 0.75" diameter.