

10X Objective, Nikon CFI Super Fluor

See More by [Nikon](#)



Stock #88-375 3-4 DAYS

- 1 + **€5.113,00**

ADD TO CART

Qty 1+
€5.113,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Field of View (mm):
2.20

Horizontal Field of View, 1/2" Sensor:
0.64mm

Horizontal Field of View, 2/3" Sensor:
0.88mm

Model Number:

MRF00101
Length (mm): 58.70
Length excluding Threads (mm): 58.70
Magnification: 10X
Maximum Diameter (mm): 32
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.50
Mounting Threads: M25 x 0.75
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Working Distance (mm): 1.2
Weight (g): 168.00
Style: Infinity Corrected
Manufacturer: Nikon
Field Number (mm): 22
Parfocal Length (mm): 59.9
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View