

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

80.5mm Max. Aperture, Iris Diaphragm



Stock #32-613 □ In Stock



1



€320,00

ADD TO CART

Qty 1-4

€320,00

Qty 5+

€282,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
4.5

Maximum Aperture (mm):
80.5

Outer Diameter (mm):

110.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 13.00
Number of Leaves: 16.00
Thickness (mm): 10.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)