

113mm Dia x 272mm FL Alum. Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#68-798** [CONTACT US](#)



1



€392,00

ADD TO CART

Qty 1-10

€392,00

Qty 11+

€342,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: 

Coating:
Protected Aluminum (400-700nm)

Coating Specification:
Ravg >85% @400 - 700nm

Coating Type: Metal
Center Hole Diameter (mm): 27.0
Height (mm): 54.0
Inner Diameter (mm): 109
Outer Diameter (mm): 113.00 +0.0/-0.5
Type: Specialty Mirror
Wavelength Range (nm): 400 - 700
Distance to Focal Point f₁ (mm) : 17
Distance to Focal Point f₂ (mm): 272

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
