

113mm Dia x 272mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#68-801** [CONTACT US](#)



1



€521,00

ADD TO CART

Qty 1-10

€521,00

Qty 11+

€461,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: 

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm): 27.0
Height (mm): 54.0
Inner Diameter (mm): 109
Outer Diameter (mm): 113.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f_1 (mm) : 17
Distance to Focal Point f_2 (mm): 272

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View

